

Lenses Fixed Focal Lenses Basler Lenses C-Mount Lenses

Basler Lens C10-1214-2M-S

Basler Standard **C-mount lens** with a fixed focal length of 12.5 mm, aperture range from F1.4–F16, and a resolution of 2 MP.



Key Features

- Fits all Basler cameras with a sensor size of up to 1"
- Metal housing
- C-mount
- Locking screws for iris and focus

i Info

The technical data shown in the following sections are nominal design values. The real values of the delivered products can deviate from the nominal design values.

General Specifications

	C10-1214-2M-S
Order Number	2200000099
Focal Length f'	12.7 mm \pm 5 %

	C10-1214-2M-S
Aperture Range	F1.4–F16
Image Circle	16 mm (1" format)
Focus Range	0.1 m to infinity
Optimum Working Distance	1.0 m
Relative Illumination at Full Aperture	41 % (see Simulated Relative Illumination versus Image Height)
Resolution (25 % MTF, Full Aperture)	Designed for 64 LP/mm (7.5 μm pixel size, see Measured Resolution versus Image Height)
Optical Distortion	Typical -5.93 % (see Simulated Distortion versus Image Height)
Angle of View, 1" Format	Horizontal: 56.45° Vertical: 42.51°
Angle of View, 1/1.2" Format	Horizontal: 49.6° Vertical: 31.73°
Wavelength Range	Visible (400–700 nm)
Pupil Magnification, β'_p	50.6
Chief Ray Angle, CRA	6.7°
Front Focal Length, s_F	12.49 mm
Back Focal Length, s'_F	12.55 mm
Principal Point Separation, HH'	29.49 mm
Entrance Pupil Position,	14.67 mm


C10-1214-2M-S	
s_{EP}	
Overall Optical Length, d	67.38 mm

→ See [Terminology \(Basler Lenses\)](#).

Mechanical Specifications

C10-1214-2M-S	
Flange Back	17.526 mm
Mount	C-mount
Weight	Approx. 175 g
Focus/Iris Operation	Manual Operating angle: 258.3°

Lens Dimensions



Not to scale
Dimensions in mm

→ Download the [CAD/technical drawing for your Basler Lens](#) .

Precautions, Mounting, and Cleaning (Basler Lenses)


→ See [Precautions, Mounting, and Cleaning \(Basler Lenses\)](#).

Environmental Requirements


Temperature During Operation	-10–50 °C (14–122 °F) (For best results, adjust the focus when a steady operating temperature has been reached.)
Humidity During Operation	20–80 % relative humidity, non-condensing
Temperature During Storage	-20–60 °C (-4–140 °F)
Humidity During Storage	20–70 % relative humidity, non-condensing

Performance Charts

Simulated Relative Illumination versus Image Height




Simulated Distortion versus Image Height



Measured Resolution versus Image Height

Conditions: $f/1.4$, polychromatic, 1.0 m working distance, average result based on 10 samples



Was this page helpful?

